

ANALOGUE INDOOR CLOCK

SLH-OP

The model series SLH-OP is optimally suited for the use in operating theaters, clean room environments, chemical plants, laboratories, swimming and fitness centers, as well as the food and beverage industry, canteen kitchens etc.




JUST A FEW STEPS TO YOUR SLH-OP

To make sure your SLH-OP meets all your requirements, you can assemble the components individually. Naturally, our experts will be happy to help.

1. With or without digital display?

CONFIGURATION

Optionally, the SLH-OP is available with an additional digital display. This display can be used as a time, date or temperature display or as a stopwatch.



SLH-OP



SLH-OPD

2. Pick your time code variant:

TIME CODE

Code	Time code	Ø	Power supply	Hands	Movement	Max. power consumption	Accuracy (synchronized)	Loss of signal
MOBALINE SELF-SETTING: MXX								
SAM	MOBALine	25-40	MOBALine	h/m	SAM 40	< 6mA @ 17VAC (0.1W)	< +/- 100ms	12:00 position after 24 hours
SEM	MOBALine	25-40	MOBALine	h/m/s	SEM 40			
NTP (LAN) SELF-SETTING (WITH UNICAST AND MULTICAST): NXX								
SAN	NTP	25-40	PoE	h/m	SAN 40	PoEclass 1: <1.9W ¹ / <3.8W ²	< +/- 50ms	12:00 position after 24 hours
SEN	NTP	25-40	PoE	h/m/s	SEN 40			
POLARIZED IMPULSES: IXX								
A	Min. impulse	25-30	24-48V impulse	h/m	AA0	6mA @ 48VDC (0.3W)	-	Standstill
SEI	Sec. impulse	25-40	24-60V impulse	h/m/s	SEI 40	-	-	Standstill

¹ single-sided clock ² cascaded double-sided clock

3.

Which installation solution works?

INSTALLATION



N
Wall mounting



F
Flush mounting

4. Which dial design do you like?

DIAL

The SLH-OP offers the following standard design options. For logo prints, please contact our customer service.



dial 300



dial 310

Additional steps limited to configure SLH-OPD clocks:

5.

Choose your display color

DISPLAY COLOR

(SLH-OPD only) The display background is black, offering optimal display contrast. The digit color is selectable. The available variants:



6. Which version do you need?

VERSION

(SLH-OPD only) For the digital clock, the following synchronization and power supply versions are available:

CODE	SYNCHRONIZATION	POWER SUPPLY
STD	autonomous/MOBALine	24VDC
PoE	NTP	PoE
PoEclass	NTP	PoE (IEEE 802.3af class 3)

YOUR SLH-OP IS COMPLETE

You can now order your SLH-OP and calculate the corresponding code. Enter the abbreviation for each component of your choice in the bright field and find your SLH-OP code. It serves as the order code or as the foundation for further steps.

- 1. Configuration Code
- 2. Time code Code
- 3. Installation Code
- 4. Dial Code
- 5. Display color Code
- 6. Version Code

Example order code



1.	2.	3.	4.	5.	6.
SLH-OP	SEM	F	300	.	.
	movement SEM 40	flush mounting	dial 300	not used ¹	not used ¹

¹ only required with the SLH-OPD

Standards

Depending on the movement used in your SLH-OP clock, the following standards apply:


MOVEMENT(S)	STANDARDS
SAM 40 SEM 40 SAN 40 SEN 40	2011/65/EU / 2014/30/EU / 2014/35/EU / 2016/797/EU EN 50121-4 / EN 60950-1 / EN 61000-6-2 / EN 61000-6-3
SEI 40	2011/65/EU / 2014/30/EU / 2014/35/EU / EN 61000-6-2 EN 61000-6-3

All SLH-OP clocks are compliant with CE, RoHS and REACH.

TECHNICAL DATA

TECHNICAL DATA		SLH-OP	SLH-OPD
General			
Degree of protection	IP 54		
Housing	aluminium		
Weight (kg)	5	7	
Analogue clock			
Diameter (mm)	248		
Reading distance (m)	20-25*		
Operating conditions	-30 to +70 °C (0 to 95% relative humidity, non-condensing)		
Digital clock (SLH-OPD)			
Digit height (mm)	-	38	
Time format	-	HH:MM:SS	
Reading distance (m)	-	15-22*	
Power supply	-	Standard: 100 – 240 VAC, 50 – 60 Hz VDC (on request): 18 – 56 VDC (18 – 40 VAC) PoE version: PoE (IEEE 802.3af class 0)	
Quartz accuracy at 20 °C	-	Without synchronization: ±0.3 seconds/day	
Quartz-based time maintenance (without power supply)	Mains power supply	-	From lithium battery: > 6 years
	PoE version	-	No time maintenance (> 12 hours from SuperCap on request)
Temperature precision	-	-25 to +85 °C: ±0.5 °C, -50 to +125 °C: ±2.0 °C	
Operating conditions	-	0 to +50 °C (0 to 95% relative humidity, non-condensing)	

* The reading distance varies depending on the dial, lighting, viewing angle, etc.



All dimensions in mm.

LE-801310.23 / 2022

*Do you have any questions?
We are happy to help.*

Moser-Baer AG | Spitalstrasse 7 | CH-3454 Sumiswald
Tel. +41 34 432 46 46 | Fax +41 34 432 46 99
info@mobatime.com | www.mobatime.com



Product specifications are subject to change without notice.